


QUICKTRONIC INTELLIGENT DALI DIM T5

ECG dimmable DALI for FL 16 mm



Product family features

- Corridor function for direct connection of ECG to common motion sensor
- Corridor function with pre-programmed light program
- Touch DIM function for free parameterization of light value and turn on time
- Fit for SMART GRID for feedback of consumed mains power and lamp operating hours
- Fit for emergency function for automatic detection of emergency lighting by ECG
- Very low standby power consumption: < 0.5 W
- Lifetime: > 100,000 h (for $T = 65^{\circ}\text{C}$ at T_c)
- Very high number of switching cycles: up to 300,000
- Dimming range: 1...100 % (3...100 % with compact fluorescent lamp)
- POWER2LAMP function for optimal matching of ECG power to lamp during lamp lifetime
- Line frequency: 0 Hz, 50...60 Hz, rectified AC

Product family benefits

- System+ Guarantee available
- Easy integration in luminaire thanks to same dimensions like DALI GI ECG
- TouchDIM function for easy and inexpensive dimming of several ECGs
- Same luminous flux with direct and alternating current
- Dimming of amalgam lamps without flickering or reduced lifespan
- Automatic restart after lamp replacement

DALI product features

- Control via the DALI interface
- Compliance with the DALI Version-1 and IEC 60929
- Control input protected against overvoltage and polarity reversal (OSRAM ECG)

Touch DIM and Touch DIM Sensor function

- Manual dimming without controller and with standard switches
- Including memory function (double click) and soft start

Product family datasheet

Areas of application

- Suitable for use in emergency lighting systems as per EN 50172/DIN VDE 0108-100
- Installation in emergency lighting systems according to IEC 61347-2-3, appendix J
- Industry
- Open-plan offices, corridors and storage rooms
- Public buildings
- Sports halls and factories
- Strip lighting
- Shop lighting
- Suitable for luminaires of protection class I

Product family datasheet

Technical data

	Electrical data				Light technical data	Dimensions & weight
Product description	Input voltage AC	Nominal voltage	Mains frequency	Input voltage DC	Starting time	Length
QTi DALI 2X35/49 DIM	198...264 V	220...240 V	50...60 Hz	154...276 V	06 s ¹⁾	3600 mm
QTi DALI 3X14/24 DIM	198...264 V	220...240 V	50...60 Hz	154...276 V	06 s ¹⁾	3600 mm

Product description	Width	Height	Mounting hole spacing, length	Product weight	Cable cross-section, output side	Cable cross-section, input side
QTi DALI 2X35/49 DIM	300 mm	210 mm	415.0 mm	30500 g	0.5...1.5 / 0.5...1.0 mm ² ²⁾	0.5...1.5 / 0.5...1.0 mm ² ²⁾
QTi DALI 3X14/24 DIM	400 mm	210 mm	350.0 mm	38600 g	0.5...1.5 / 0.5...1.0 mm ² ²⁾	0.5...1.5 / 0.5...1.0 mm ² ²⁾

	Temperatures & operating conditions	Lifespan	Capabilities		
Product description	Ambient temperature range	ECG lifetime	Dimmable	Suitable for fixtures with prot. class	End of lamp life safety shutdown
QTi DALI 2X35/49 DIM	+10...+50 °C	100000 h ³⁾	Yes	I	EOL T.2
QTi DALI 3X14/24 DIM	+10...+50 °C	100000 h ³⁾	Yes	I	EOL T.2

	Certificates & standards		Logistical data	Environmental information Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)
Product description	Approval marks – approval	Protection class	Commodity code	Date of Declaration
QTi DALI 2X35/49 DIM	VDE / VDE-EMC / EL I / EAC / RCM / CCC		850410809000	26-04-2024
QTi DALI 3X14/24 DIM	VDE / VDE-EMC / EL I / EAC / RCM / CCC		85041080900	07-07-2023

Product description	Primary Article Identifier	Candidate List Substance 1	CAS No. of substance 1	Safe Use Instruction
QTi DALI 2X35/49 DIM	4050300870465	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.

Product family datasheet

Product description	Primary Article Identifier	Candidate List Substance 1	CAS No. of substance 1	Safe Use Instruction
QTi DALI 3X14/24 DIM	4008321069955	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.

Product description	Declaration No. in SCIP database
QTi DALI 2X35/49 DIM	54e21b39-5873-42c2-b23e-0380acb761b4
QTi DALI 3X14/24 DIM	9172d239-c01b-4170-9a8b-3f8d5b223615

1) Optimized preheat start
2) Solid leads
3) At $T_{case} = 65^{\circ}C$ at T_c point / 10% failure rate

Product family datasheet

Application advice

For more detailed application information and graphics please see product datasheet.

Additional product information

- In order to achieve good radio interference suppression:1. Keep the cable between ECG and lamp as short as possible.2. The single lamp wires must be routed as close as possible to each other, whereas the lines of the different lamp ends must be routed separately.

Sales and Technical Support

Sales and Technical Support www.osram.com

Country specific information

Product description	Product code	METEL code	SEG-No.	STK-Number	UK Org
QTi DALI 2X35/49 DIM	4050300870403	OSRQTIDALI1X18	-	-	-
QTi DALI 2X35/49 DIM	4050300870403	OSRQTIDALI1X18	-	-	-
QTi DALI 3X14/24 DIM	4008321069955	OSRQTIDALI3X1424	-	-	-
QTi DALI 3X14/24 DIM	4008321069955	OSRQTIDALI3X1424	-	-	-

Download Data

File	
	User instruction QUICKTRONIC QTi T5 DALI DIM
	Addon Technical Information 502689_Frequent switching Quicktronic
	Addon Technical Information 502785_ECG lifetime - QUICKTRONIC (DALI) DIM
	Certificates 335097_INOTEC
	Certificates QTI DALI VDE 40021252 210920
	Certificates 335135_Manufacturer's declaration – Burning-in of fluorescent lamps
	Certificates 335153_Manufacturer's declaration – Low stand-by

Product family datasheet

	Certificates 335154_Manufacturer's declaration – EN 55015:2006+A1:2007 (300 MHz)
	Certificates 335169_Manufacturer's declaration – LampECG combinations: Frequent switching
	Certificates 592319_EAC certificate for Quicktronics QT
	Certificates 504208_VDE-EMC-CERTIFICATE QTl DALI DIM
	Declarations of conformity QUICKTRONIC DIM CE 3364258 060923
	Operating instructions 592411_EAC QTl T5 DALI DIM
	CAD data 3-dim 313428_423x30x21 1881282
	CAD data 3-dim 313430_423x30x21 1881282
	CAD data 3-dim 313444_423x30x21 1881282
	CAD data PDF 313416_423x30x21 1881282
	CAD data 3-dim 313451_360x40x21 9900042
	CAD data 3-dim 313478_360x40x21 9900042
	CAD data 3-dim 314276_360x40x21 9900042
	CAD data PDF 313387_360x40x21 9900042

Ecodesign regulation information:

Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300870403	QTl DALI 2X35/49 DIM	Shipping carton box 20	392 mm x 98 mm x 165 mm	6.34 dm ³	6319.99 g

Product family datasheet

Logistical Data

4008321069955	QTi DALI 3X14/24 DIM	Shipping carton box 20	380 mm x 206 mm x 96 mm	7.51 dm ³	8673.00 g
---------------	----------------------	---------------------------	-------------------------	----------------------	-----------

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For more information on the system guarantee and the terms and conditions of the guarantee visit <https://www.inventronics-light.com/multilevel-guarantees>

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.